

## QN18M18X02D, Nylon Male Quick Disconnect For 22 - 18 AWG (.19 x .02)

By Burndy  
Catalog # [QN18M18X02D](#)



Nylon Male Quick Disconnect For 22 - 18 AWG (.19 x .02).

### Features

- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Mates with dimpled female socket detent ensuring firm grip

### Application

For quickly connecting or disconnecting a terminal

### General

Catalog Number	QN18M18X02D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293300
UPC 12 Digit	7818102933000

### Dimensions

Dimension - Length Overall inch	0.8 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

### Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

### Conductor Related

Conductor Range	#22 AWG to #16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

### Product Assets

[3D Models - QN18M18X02D\\_MODEL-IGES](#)  
[3D Models - QN18M18X02D\\_MODEL-PDF](#)  
[3D Models - QN18M18X02D\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_L6FQNM\\_LineArt](#)  
[Sales Drawings - 50094209](#)  
[Specifications - QN18M18X02D](#)