



## QN18M25X03D, Nylon Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [QN18M25X03D](#)



Nylon Male Quick Disconnect For 22 - 18 AWG (.25 x .03).

### Features

- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Mates with dimpled female socket detent ensuring firm grip

### Application

Male Disconnect

### General

|                   |                       |
|-------------------|-----------------------|
| Catalog Number    | QN18M25X03D           |
| Connector Type    | Male Quick Disconnect |
| EU RoHS Indicator | Yes                   |
| Insulation        | Y                     |
| Insulation Type   | Nylon                 |
| Material          | Brass                 |
| Plated            | Y                     |
| Plating Type      | Tin                   |
| Sub Brand         | FINGRIP               |
| Trade Name        | FINGRIP™              |
| Type              | Disconnect Connectors |
| UPC               | 781810293324          |
| UPC 12 Digit      | 7818102933244         |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Length Overall inch | 0.87 in |
| Dimension - Strip Length inch   | 3/8 in  |
| Dimension - Width inch          | 0.25 in |
| Dimension - Width mm            | 6 mm    |

### Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 300 V |
|-------------------|-------|

### Conductor Related

|                 |                    |
|-----------------|--------------------|
| Conductor Range | #22 AWG to #16 AWG |
| Conductor Size  | 22 - 18 AWG        |
| Conductor Type  | CU C Str-Size      |

### Certifications And Compliance

|                                    |       |
|------------------------------------|-------|
| Buy American Compliant             | Yes   |
| Certification - CSA Approved       | No    |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM    |
| UL Listed                          | No    |

### Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 1200  |
| Minimum Pack Quantity | 100   |
| Pallet Quantity       | 99999 |

### Product Assets

- [3D Models - QN18M25X03D\\_MODEL-IGES](#)
- [3D Models - QN18M25X03D\\_MODEL-STEP](#)
- [3D Models - QN18M25X03D\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094209](#)
- [Specifications - QN18M25X03D](#)