



QP10M250D, Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [QP10M250D](#)



Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03).

General

Catalog Number	QP10M250D
Connector Type	Male Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810020647
UPC 12 Digit	7818100206477

Dimensions

Dimension - D inch	0.35 in
Dimension - Length Overall inch	1.12 in
Dimension - N inch	0.18 in
Dimension - Pad Width inch	0.25 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KPFQPM_LineArt](#)
[Specifications - QP10M250D](#)