



QP10M25X03D, Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [QP10M25X03D](#)



Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03).

Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

Male Disconnect

General

Catalog Number	QP10M25X03D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525067
UPC 12 Digit	7818105250677

Dimensions

Dimension - Length Overall inch	0.93 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

- [3D Models - QP10M25X03D_MODEL-IGES](#)
- [3D Models - QP10M25X03D_MODEL-STEP](#)
- [3D Models - QP10M25X03D_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KPFQPM_LineArt](#)
- [Sales Drawings - 50094206](#)
- [Specifications - QP10M25X03D](#)



A Hubbell brand