



# Vinyl Female Quick Disconnect For 16 - 14 AWG (.11 x .02)

By Burndy  
Catalog # [QP14F11X02D](#)



Vinyl Female Quick Disconnect For 16 - 14 AWG (.11 x .02).

## Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

## Application

Female Disconnect

## General

Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810480267
UPC 12 Digit	7818104802677

## Dimensions

Dimension - Length Overall inch	0.75 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor Range #14 AWG to #16 AWG  
Conductor Size 16 - 14 AWG  
Conductor Type CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved No  
Certification - ETL No  
Certification - UL Recognized No  
Certification - cULus Yes  
Industry Standard(s) UL467  
Standards - Industry UL310  
Standards Met  
Standards - RoHS Compliance CM  
Status  
UL Listed No

## Logistics

Carton Quantity 1200  
Minimum Pack Quantity 100

## Product Assets

[3D Models - QP14F11X02D\\_MODEL-STEP](#)  
[3D Models - QP14F11X02D\\_MODEL-PDF](#)  
[3D Models - QP14F11X02D\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094207](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-QP14F11X02D-SPEC-EN | REV 5/2024