



## QP14F18X02D, Vinyl Female Quick Disconnect For 16 - 14 AWG (.19 x .02)

By Burndy  
Catalog # [QP14F18X02D](#)



Vinyl Female Quick Disconnect For 16 - 14 AWG (.19 x .02).

### Application

For quickly connecting or disconnecting a terminal

### General

|                   |                         |
|-------------------|-------------------------|
| Catalog Number    | QP14F18X02D             |
| Connector Type    | Female Quick Disconnect |
| EU RoHS Indicator | Yes                     |
| Insulation        | Y                       |
| Insulation Type   | Vinyl                   |
| Material          | Brass                   |
| Plated            | Y                       |
| Plating Type      | Tin                     |
| Sub Brand         | FINGRIP                 |
| Trade Name        | FINGRIP™                |
| Type              | Disconnect Connectors   |
| UPC               | 781810293379            |
| UPC 12 Digit      | 7818102933799           |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Length Overall inch | 0.79 in  |
| Dimension - Strip Length inch   | 3/8 in   |
| Dimension - Width inch          | 0.187 in |
| Dimension - Width mm            | 5 mm     |

### Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

### Conductor Related

|                 |                    |
|-----------------|--------------------|
| Conductor Range | #14 AWG to #16 AWG |
| Conductor Size  | 16 - 14 AWG        |

Conductor Type CU C Str-Size

### Certifications And Compliance

|                                |       |
|--------------------------------|-------|
| Buy American Compliant         | Yes   |
| Certification - CSA Approved   | No    |
| Certification - ETL            | No    |
| Certification - UL Recognized  | No    |
| Certification - cULus          | Yes   |
| Industry Standard(s)           | UL467 |
| Standards - Industry Standards | UL310 |
| Met                            |       |
| Standards - RoHS Compliance    | CM    |
| Status                         |       |
| UL Listed                      | No    |

### Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 1200  |
| Minimum Pack Quantity | 100   |
| Pallet Quantity       | 99999 |

### Product Assets

[3D Models - QP14F18X02D\\_MODEL-STEP](#)  
[3D Models - QP14F18X02D\\_MODEL-PDF](#)  
[3D Models - QP14F18X02D\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KPFQPF\\_LineArt](#)  
[Sales Drawings - 50094207](#)  
[Specifications - QP14F18X02D](#)