

## QP14F25X03B, Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy  
Catalog # [QP14F25X03B](#)



Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03).

### Application

For quickly connecting or disconnecting a terminal

### General

Catalog Number	QP14F25X03B
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292754
UPC 12 Digit	7818102927544

### Dimensions

Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KQF\\_LineArt](#)  
[Sales Drawings - 50094207](#)  
[Specifications - QP14F25X03B](#)