

QP14F25X03BG25, Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy

Catalog # [QP14F25X03BG25](#)



Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03).

Application

For quickly connecting or disconnecting a terminal

General

Catalog Number	QP14F25X03BG25
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810486238

Dimensions

Dimension - B Length fraction	1/5 in
Dimension - B Length inch	0.20 in
Dimension - F Width Center to Center inch	0.08 in
Dimension - Length Overall inch	0.85 in
Dimension - Width inch	0.26 in

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
-----------------------------	---------------

Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_QP10F25X03BG25_LineArt](#)
- [Sales Drawings - 10104489](#)
- [Specifications - QP14F25X03BG25](#)