

QP14M11X02D, Vinyl Male Quick Disconnect For 16 - 14 AWG (.11 x .02)

By Burndy
Catalog # [QP14M11X02D](#)



Vinyl Male Quick Disconnect For 16 - 14 AWG (.11 x .02).

Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

Male Disconnect

General

Catalog Number	QP14M11X02D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810530672
UPC 12 Digit	7818105306722

Dimensions

Dimension - Length Overall inch	0.76 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100

Product Assets

[3D Models - QP14M11X02D_MODEL-IGES](#)
[3D Models - QP14M11X02D_MODEL-STEP](#)
[3D Models - QP14M11X02D_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094206](#)
[Specifications - QP14M11X02D](#)