

QP14M18X02D, Vinyl Male Quick Disconnect For 16 - 14 AWG (.19 x .02)

By Burndy
Catalog # [QP14M18X02D](#)



Vinyl Male Quick Disconnect For 16 - 14 AWG (.19 x .02).

Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

For quickly connecting or disconnecting a terminal

General

Catalog Number	QP14M18X02D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293461
UPC 12 Digit	7818102934611

Dimensions

Dimension - Length Overall inch	0.76 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100

Product Assets

[3D Models - QP14M18X02D_MODEL-PDF](#)
[3D Models - QP14M18X02D_MODEL-IGES](#)
[3D Models - QP14M18X02D_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KPFQPM_LineArt](#)
[Sales Drawings - 50094206](#)
[Specifications - QP14M18X02D](#)