



QP14M25X03B, Vinyl Male Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # [QP14M25X03B](#)



Vinyl Male Quick Disconnect For 16 - 14 AWG (.25 x .03).

Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

General

| | |
|-----------------|-----------------------|
| Catalog Number | QP14M25X03B |
| Connector Type | Male Quick Disconnect |
| Insulation | Y |
| Insulation Type | Vinyl |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | FINGRIP™ |
| Type | Disconnect Connectors |
| UPC | 781810292822 |
| UPC 12 Digit | 7818102928222 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Length Overall inch | 0.84 in |
| Dimension - Strip Length inch | 3/8 in |
| Dimension - Width inch | 0.25 in |
| Dimension - Width mm | 6 mm |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

Conductor Related

| | |
|-----------------|---|
| Conductor Range | #14 AWG to #16 AWG |
| Conductor Size | 16 - 14 AWG |
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |

Certifications And Compliance

| | |
|--------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | Yes |
| Standards - Industry Standards | UL310 |
| Met | |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 1000 |
| Minimum Pack Quantity | 1000 |
| Pallet Quantity | 99999 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094206](#)
[Specifications - QP14M25X03B](#)