



QP18F11X02D, Vinyl Female Quick Disconnect For 22 - 18 AWG (.11 x .02)

By Burndy  
Catalog # QP18F11X02D

Vinyl Female Quick Disconnect For 22 - 18 AWG (.11 x .02).

Application

Female Disconnect

General

Catalog Number	QP18F11X02D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810480250
UPC 12 Digit	7818104802500

Dimensions

Dimension - Length Overall inch	0.75 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #22 AWG
-----------------	--------------------

Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100

Product Assets

- 3D Models - QP18F11X02D\_MODEL-STEP
- 3D Models - QP18F11X02D\_MODEL-PDF
- 3D Models - QP18F11X02D\_MODEL-IGES
- Catalogs - BURNDY Master Catalog - Section B - Small Compression
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Sales Drawings - 50094207
- Specifications - QP18F11X02D