



## QP18F18X02D, Vinyl Female Quick Disconnect For 22 - 18 AWG (.19 x .02)

By Burndy  
Catalog # [QP18F18X02D](#)



Vinyl Female Quick Disconnect For 22 - 18 AWG (.19 x .02).

### Application

For quickly connecting or disconnecting a terminal

### General

Catalog Number	QP18F18X02D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293171
UPC 12 Digit	7818102931711

### Dimensions

Dimension - Length Overall inch	0.79 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#16 AWG to #22 AWG
Conductor Size	22 - 18 AWG

Conductor Type CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

### Product Assets

- [3D Models - QP18F18X02D\\_MODEL-STEP](#)
- [3D Models - QP18F18X02D\\_MODEL-PDF](#)
- [3D Models - QP18F18X02D\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_KPFQPF\\_LineArt](#)
- [Sales Drawings - 50094207](#)
- [Specifications - QP18F18X02D](#)