

QP18F25X03BG25, Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy

Catalog # [QP18F25X03BG25](#)



Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

General

Catalog Number	QP18F25X03BG25
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810486252

Dimensions

Dimension - B Length fraction	1/5 in
Dimension - B Length inch	0.20 in
Dimension - F Width Center to Center inch	0.08 in
Dimension - Length Overall inch	0.87 in
Dimension - Width inch	0.26 in

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_QP10F25X03BG25_LineArt](#)
- [Sales Drawings - 10104489](#)
- [Specifications - QP18F25X03BG25](#)