

## QP18M25X03B, Vinyl Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [QP18M25X03B](#)



Vinyl Male Quick Disconnect For 22 - 18 AWG (.25 x .03).

### Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

### General

Catalog Number	QP18M25X03B
Connector Type	Male Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292716
UPC 12 Digit	7818102927166

### Dimensions

Dimension - Length Overall inch	0.84 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#16 AWG to #22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50094206](#)  
[Specifications - QP18M25X03B](#)