

QP18M25X03D, Vinyl Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [QP18M25X03D](#)



Vinyl Male Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

For quickly connecting or disconnecting a terminal

General

| | |
|-------------------|-----------------------|
| Catalog Number | QP18M25X03D |
| Connector Type | Male Quick Disconnect |
| EU RoHS Indicator | Yes |
| Insulation | Y |
| Insulation Type | Vinyl |
| Material | Brass |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | FINGRIP |
| Trade Name | FINGRIP™ |
| Type | Disconnect Connectors |
| UPC | 781810293294 |
| UPC 12 Digit | 7818102932944 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Length Overall inch | 0.84 in |
| Dimension - Strip Length inch | 3/8 in |
| Dimension - Width inch | 0.25 in |
| Dimension - Width mm | 6 mm |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

Conductor Related

| | |
|-----------------|--------------------|
| Conductor Range | #16 AWG to #22 AWG |
| Conductor Size | 22 - 18 AWG |
| Conductor Type | CU C Str-Size |

Certifications And Compliance

| | |
|--------------------------------|---|
| Buy American Compliant | Contact Manufacturer |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | Yes |
| Certified Listed | TAA Compliant (All status valid till December 2024) |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards | UL310 |
| Met | |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 1200 |
| Minimum Pack Quantity | 100 |
| Pallet Quantity | 99999 |

Product Assets

- [3D Models - QP18M25X03D_MODEL-PDF](#)
- [3D Models - QP18M25X03D_MODEL-STEP](#)
- [3D Models - QP18M25X03D_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KPFQPM_LineArt](#)
- [Sales Drawings - 50094206](#)
- [Specifications - QP18M25X03D](#)