



# Tin Plated Heavy Duty Copper Tapping Connector

By Burndy  
Catalog # [QPX2828Y](#)

VERSITAP™ Mechanical Parallel Clamp for Copper and Aluminum; Run: 1/0 - 4/0 Str; Tap: 1/0 - 4/0 Str; 2" Length; 2-1/8" Width



## Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

## Application

For Use With Copper Or Aluminum Cable

## General

|                                       |                          |
|---------------------------------------|--------------------------|
| Catalog Number                        | QPX2828Y                 |
| Connector Type                        | Universal Clamp          |
| EU RoHS Indicator                     | Yes                      |
| Installation Torque Recommended in-lb | 250 LBS/in               |
| Material                              | Copper                   |
| Material - Hardware Plated            | DURIUM™ Silicon Bronze Y |
| Plating Type                          | Tin                      |
| Sub Brand                             | VERSITAP                 |
| Trade Name                            | VERSITAP™                |
| Type                                  | QPX-Y, Universal         |
| UPC                                   | 781810342404             |

## Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Height fraction     | 2 in     |
| Dimension - Height inch         | 2.00 in  |
| Dimension - L Length Overall mm | 51 mm    |
| Dimension - Length Overall inch | 2.00 in  |
| Dimension - Width fraction      | 2-1/8 in |
| Dimension - Width inch          | 2.14 in  |
| Dimension - Width mm            | 54 mm    |

## Conductor Related

|                                  |   |
|----------------------------------|---|
| Conductor - AL Str Run           | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG   |
| Conductor - AL Str Run Range     | 1/0 AWG-4/0 AWG   |
| Conductor - AL Str Tap           | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG   |
| Conductor - AL Str Tap Range     | 1/0 AWG-4/0 AWG   |
| Conductor - Copper Str Run       | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG  |
| Conductor - Copper Str Run Range | 1/0 -4/0 AWG  |
| Conductor - Copper Str Tap       | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG  |
| Conductor - Copper Str Tap Range | 1/0 -4/0 AWG  |
| Conductor Type                   | <ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul> |

## Certifications And Compliance

|   |    |
|---|----|
| Certification - CSA Approved            | No |
| Certification - ETL                     | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized           | No |
| Certification - cULus                   | No |
| Standards - RoHS Compliance Status      | EX |
| UL Listed                               | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[3D Models - QPX2828Y\\_MODEL-STEP](#)  
[3D Models - QPX2828Y\\_MODEL-IGES](#)  
[3D Models - QPX2828Y\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_QPX\\_PARA\\_CLAMP\\_LineArt](#)  
[Sales Drawings - sd..026550](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-QPX2828Y-SPEC-EN | REV 6/2024