

QPX2C2CY, Tin Plated Heavy Duty Copper Tapping Connector, Run: #6-#2 Str; Tap: #6-#2 Str

By Burndy

Catalog # [QPX2C2CY](#)



VERSITAP™ Mechanical Parallel Clamp for Copper and Aluminum; Run: #6 - #2 Str; Tap: #6 - #2 Str.

Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Use With Copper Or Aluminum Cable

General

Catalog Number	QPX2C2CY
Connector Type	Universal Clamp
EU RoHS Indicator	Yes
Installation Torque	150 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX-Y, Universal
UPC	781810341803
UPC 12 Digit	7818103418033

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.52 in
Dimension - Height fraction	1-5/8 in
Dimension - Height inch	1.59
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in

Dimension - Width fraction	1-5/8 in
Dimension - Width inch	1.61
Dimension - Width mm	41 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	24
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

Catalogs - BURNDY Master Catalog - Section A - Mechanical
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) -
BUR_QPX_PARA_CLAMP_LineArt
Sales Drawings - sd..026550
Specifications - QPX2C2CY



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QPX2C2CY-SPEC-EN | REV 10/2024