

# QPX4444L, Heavy Duty Copper Tapping Connector

By Burndy  
Catalog # [QPX4444L](#)



VERSITAP™.

## General

Catalog Number	QPX4444L
Connector Type	Universal Clamp
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	4
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810162385
UPC 12 Digit	7818101623855

## Dimensions

Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil
Conductor - Copper Str Tap	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	500 kcmil-1000 kcmil
Conductor - Nominal Diameter	0.813, 0.893, 0.893, 0.964, 0.998, 1.031, 1.031, 1.094, 1.151
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	11
-----------------------	----

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) -](#)

[BUR\\_QPX\\_PARA\\_CLAMP\\_LineArt](#)

[Specifications - QPX4444L](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-QPX4444L-SPEC-EN | REV 8/2024