

# QPX4444Y, Tin Plated Heavy Duty Copper Tapping Connector, Run: 750-1000 kcmil; Tap: 250-500 kcmil

By Burndy  
Catalog # [QPX4444Y](#)



VERSITAP™ Mechanical Parallel Clamp for Copper and Aluminum; Run: 750 - 1000 kcmil; Tap: 250 - 500 kcmil.

## Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

## General

Catalog Number	QPX4444Y
Connector Type	Universal Clamp
Installation Torque	500 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810006146
UPC 12 Digit	7818100061466

## Dimensions

Dimension - Height fraction	3-7/8 in
Dimension - Height inch	3.78
Dimension - Height mm	96 mm
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in
Dimension - Width fraction	3-1/2 in
Dimension - Width inch	3.5
Dimension - Width mm	89 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - AL Str Run	750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Run Range	750 kcmil-1000 kcmil
Conductor - AL Str Tap	750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Tap Range	750 kcmil-1000 kcmil
Conductor - Copper Str Run	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Tap	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	750 kcmil-1000 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	4
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand