

QR28, Heavy Duty Copper Splice Reducer

By Burndy
Catalog # [QR28](#)



Splice or Reducer, 3/0 Str. - 4/0 Str., Recommended Tightening Torque: 250 IN-LB.

Features

- Type QR QIKLINK™ splice or reducer features a neat, compact, easy to tape installation
- One-wrench installation

General

Catalog Number	QR28
Connector Type	In-Line
Installation Torque	250 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLINK™
UPC	781810334515

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Height fraction	1-3/8 in
Dimension - Height inch	1.13 in
Dimension - Height mm	28.7 mm
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Width fraction	1 in
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - Copper Solid Size A	3/0 AWG;4/0 AWG
Conductor - Copper Solid Size A Range	3/0 AWG-4/0 AWG

Conductor - Copper Solid Size B	3/0 AWG;4/0 AWG
Conductor - Copper Solid Size B Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Size A	3/0 AWG;4/0 AWG
Conductor - Copper Str Size A Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Size B	3/0 AWG;4/0 AWG
Conductor - Copper Str Size B Range	3/0 AWG-4/0 AWG
Conductor Size	3/0-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_G4FQR_LineArt](#)
- [Sales Drawings - SA011559-01](#)
- [Specifications - QR28](#)