



Ratchet Cable Cutter, Cuts up to 1000 kcmil Copper and Aluminum, Maximum Insulation Diameter 2.375"

By Burndy
Catalog # [RCC1000](#)



Ratchet Cable Cutter, Cuts up to 1000 kcmil CU/AL, Max Ins Dia. 2.375".

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
EU RoHS Indicator	Yes
Sub Brand	RATCHET CUTTER
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810174883
UPC 12 Digit	7818101748833

Dimensions

Cable Insulation Diameter Maximum	2.375 in
Height	6 in
Length	20 in
Weight	4.5 lb

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_RCC336_LA](#)
[Sales Drawings - SE211271-01](#)



A proud member of the Hubbell Family.