

Ratchet Cable Cutter, Cuts up to 336 kcmil ACSR, up to 500 kcmil Aluminum, up to 350 kcmil Copper



By Burndy
Catalog # [RCC336](#)

Ratchet Cable Cutter, Cuts up to 336 kcmil ACSR, 500 kcmil AL, 350 kcmil CU.

Application

- Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable
Catalog Number	RCC336
EU RoHS Indicator	Yes
Sub Brand	RATCHET CUTTER
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810459980
UPC 12 Digit	7818104599800

Dimensions

Cable Insulation Diameter Maximum	1.25 in
Dimensions	10.50 in x 3.50 in x 1.25 in
Height	1.25 in

Length	10.5 in
Weight	1.2 lb
Width	3.5 in

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - Cutters](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_RCC336_LA](#)
- [Sales Drawings - 10082457](#)
- [Specifications - RCC336](#)