



# Ratchet Cable Cutter, Cuts up to 600 kcmil Soft Drawn Copper and Aluminum, Maximum Insulation Diameter 1.05"

By Burndy  
Catalog # RCC600E



Ratchet Cable Cutter, Cuts up to 600 kcmil Soft Drawn CU/AL, Max. Ins Dia. 1.05".

## Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

## Application

Cutting

## General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	RCC600E
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810488195
UPC 12 Digit	7818104881955

## Dimensions

Cable Insulation Diameter Maximum	1.05 in
Length	10.5 in
Weight	1.2 lb
Width	1.25 in

## Conductor Related

Crimping Ranges	Cutting Capacity: Copper 600 kcmil; Aluminum: 600 kcmil
-----------------	---

## Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Installation Manuals - BUR\\_30015047\\_SOMI\\_RCC600E](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30017058](#)
- [Specifications - RCC600E](#)