



Ratchet Cable Cutter, Cuts up to 954 kcmil ACSR, up to 1000 kcmil Copper and Aluminum, Maximum Insulation Dia. 1.38"

By Burndy
Catalog # RCC954ACSR1K



Ratchet Cable Cutter, Cuts up to 954 kcmil ACSR, up to 1000 kcmil CU/AL, Max. Ins. Dia. 1.38".

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable
Catalog Number	RCC954ACSR1K
EU RoHS Indicator	Yes
Sub Brand	RATCHET CUTTER
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810480595
UPC 12 Digit	7818104805955

Dimensions

Cable Insulation Diameter Maximum	1.38 in
Dimensions	22.75 in x 1.88 in x 7.00 in
Height	7 in
Length	22.75 in
Weight	6.5 lb
Width	1.88 in

Certifications And Compliance

Buy American Compliant	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_RCC336_LA](#)
- [Sales Drawings - 10098508-01_B](#)
- [Specifications - RCC954ACSR1K](#)