



Remote Hydraulic Cutter, 10000 psi, Cuts up to 2156 kcmil ACSR, up to 2.00" Copper and Aluminum

By Burndy
Catalog # [RHCC2156ACSR](#)

Remote Hydraulic Cutter, 10000 psi, Cuts up to 2156 kcmil ACSR, 2.00" CU/AL.



Features

- 180° head rotation
- Durable hardened, precision steel blades
- Specialized latch head for mid-span cuts
- Durable canvas carrying bag stores tool and accessories

Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable
Catalog Number	RHCC2156ACSR
Type	Cutter
UPC	781810671559
UPC 12 Digit	7818106715599

Dimensions

Dimension - Thread Size	-
Dimensions	13.17 in x 2.69 in x 4.13 in
Height	4.13 in
Length	13.17 in
Weight	10 lb
Width	2.69 in

Certifications And Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50025001](#)
- [Specifications - RHCC2156ACSR](#)