



Remote Hydraulic Cutter, 10000 psi, Cuts up to 2.45" O.D. Copper and Aluminum

By Burndy
Catalog # [RHCC245CUAL](#)

Remote Hydraulic Cutter, 10000 psi, Cuts up to 2.45" O.D. CU/AL.



Features

- Interference free closure for mid-span cuts
- Precision cutting blades for clean cuts
- High strength steel cylinder
- Light weight, ergonomic design
- Durable canvas carrying bag stores tool and accessories

Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	RHCC245CUAL
Tool Type	Remote Hydraulic Cutter
Type	Cutter
UPC	781810439791
UPC 12 Digit	7818104397911

Dimensions

Dimensions	14.8 in x 4.74 in x 2.45 in
Height	2.45 in
Length	14.8 in
Weight	8.4 lb
Width	4.74 in

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_RHCC245CUAL_LineArt](#)
[Sales Drawings - 10067187](#)
[Specifications - RHCC245CUAL](#)