



# Remote Hydraulic Cutter, 10000 psi, Cuts up to 4.00" O.D. Copper and Aluminum

By Burndy  
Catalog # [RHCC4CUAL](#)



Remote Hydraulic Cutter, 10000 psi, Cuts up to 4.00" O.D. CU/AL.

## Features

- Specialized scissor head design for interference free closure for mid-span cuts
- High strength hardened steel cutting blades
- 360° swivel hose fitting
- Stainless Steel lifting assist eyebolt
- Light weight ergonomic design

## Application

Cutting

## General

|                          |                        |
|--------------------------|------------------------|
| Application - For Use On | Aluminum, Copper Cable |
| Catalog Number           | RHCC4CUAL              |
| Type                     | Cutter                 |
| UPC                      | 781810665855           |

## Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 21.29 in x 5.15 in x 9.13 in |
| Height     | 9.13 in                      |
| Length     | 21.29 in                     |
| Weight     | 19.9 lb                      |
| Width      | 5.15 in                      |

## Certifications And Compliance

|                             |    |
|-----------------------------|----|
| Standards - RoHS Compliance | UI |
| Status                      |    |

## Logistics

|                       |                        |
|-----------------------|------------------------|
| Minimum Pack Quantity | 1                      |
| Package Contents      | Tool, Canvas Carry Bag |

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50024761](#)  
[Specifications - RHCC4CUAL](#)