



Convenience packaging of WIREMIKE™ (with inch markings), sold in multiples of 10 only, 4.38 in L, 1.94 in W

By Burndy
Catalog # [RK1942](#)



Wire Mike, #6 - 336.4 (26/7) str. ACSR #18 str. - 2,000 kcmil
#20 sol. - 4/0 sol., 4.38 in L, 1.52 in W.

Features

Strong, durable, high quality

Application

- Grounding

General

Catalog Number	RK1942
EU RoHS Indicator	Yes
Material	Vinyl, Textured
Sub Brand	ACCESSORY
Tool Type	WIRE MIKE COVER
Type	<ul style="list-style-type: none">• WIREMIKE• WIREMIKE
UPC	781810024409
UPC 12 Digit	7818100244099

Dimensions

Length	4.38 in
Width	1.94 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	4640

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section F - Accessories](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_RK1942_LineArt](#)
[Sales Drawings - 50015434](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-RK1942-SPEC-EN | REV 6/2024