



Ratchet Wire Rope Cutter, Cuts Mild Steel: 9/16” diameter and Stainless Steel: 1/2” diameter

By Burndy
Catalog # RWRC916



Ratchet Wire Rope Cutter, Cuts Mild Steel: 9/16” dia. and Stainless Steel: 1/2” dia.

Features

- Hardened steel blades
- Rapid blade advance
- Reduced handle force compared to scissor or compound action designs

Application

Cutting

General

Application - For Use On	Mild Steel, Stainless Steel Wire Rope
Catalog Number	RWRC916
Tool Type	Ratchet Wire Rope Cutter
Type	Cutter
UPC	781810544297
UPC 12 Digit	7818105442977

Dimensions

Length	20.75 in
Weight	4 lb
Width	6.75 in

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_RWRC916_Lineart](#)
- [Sales Drawings - 30026692-01_A](#)
- [Specifications - RWRC916](#)