



## RYA28UCR, Tap Kit - HYLUG Terminal, Rubber Sleeve, Hardware (RDM Mole)

By Burndy  
Catalog # [RYA28UCR](#)



Force Fit Rubber Sleeve Tap Kit, 4/0 Str(Al/Cu), 4/0 Str-250 Comp(Al), 249 or 840 Index.

### Application

FOR ALUMINUM OR COPPER FOR USE WITH TYPE RDM-28 URD MOLE

### General

Catalog Number	RYA28UCR
Connector Type	Terminal
Die Index	249;K-840
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Rubber
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
Sub Brand	TAP KITS, MOLE
Trade Name	MOLE™
Type	RYA-UCR
UPC	781810181959

### Dimensions

Dimension - B Length inch	1.62 in
Dimension - D inch	0.91 in
Dimension - Length Overall inch	2.74 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-11/16

### Conductor Related

Conductor - AL Str Size	4/0 AWG;250 kcmil
Conductor - AL Str Size Range	4/0 AWG-250 kcmil
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	9
Minimum Pack Quantity	1
Pallet Quantity	2160

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section K - Underground](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_RYA-AC\\_LineArt](#)  
[Sales Drawings - 63044](#)  
[Specifications - RYA28UCR](#)