

Substation - Aluminum Rigid Spacer

By Burndy

Catalog # [S2GBP41A6](#)



Two Conductor 6 IN Spacer, 715.5(24/7) kcmil-715.5(26/7) kcmil ACSR, 795 kcmil-874.5 kcmil AAC, 550kV.

Application

Substation

General

Catalog Number	S2GBP41A6
Connector Type	Spacer
Installation Torque	480 lbs-in
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810278093
UPC 12 Digit	7818102780933

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	193 mm
Dimension - Length Overall inch	7.58 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	715.5 (24/7) kcmil;715.5 (26/7) kcmil
---------------------------	---------------------------------------

Conductor - ACSR Str Size Range	715.5 (24/7) kcmil-715.5 (26/7) kcmil
Conductor - AL Str Size	795 kcmil;800 kcmil;874.5 kcmil
Conductor - AL Str Size Range	795 kcmil-874.5 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_S2GBPA_BUNDLED_SPACER_LineArt](#)
- [Sales Drawings - 30021852](#)
- [Specifications - S2GBP41A6](#)