

## Substation - Aluminum Rigid Spacer

By Burndy  
 Catalog # [S2GBP445A12](#)



### Application

Substation

### General

Catalog Number	S2GBP445A12
Connector Type	Spacer
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
UPC	781810246009
UPC 12 Digit	7818102460099

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.246 in
Dimension - Diameter Min Size inch	1.165 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Conductor Related

Conductor - ACSR Str Size	954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil
Conductor - ACSR Str Size Range	954 (45/7) Rail kcmil-1033.5 (45/7) Ortolan kcmil
Conductor - AL Str Size	1033 kcmil;1100 kcmil;1113 kcmil
Conductor - AL Str Size Range	1033 kcmil-1113 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_S2GBPA\\_BUNDLED\\_SPACER\\_LineArt](#)
- [Specifications - S2GBP445A12](#)