

Substation - Aluminum Rigid Spacer

By Burndy
 Catalog # [S2GBP445A8](#)



Two Conductor 8 IN Spacer, 954 kcmil-1033.5 kcmil ACSR,
 1033.5 kcmil-1113 kcmil AAC.

Application

Substation

General

| | |
|---------------------|----------------------|
| Catalog Number | S2GBP445A8 |
| Connector Type | Spacer |
| Installation Torque | 480 lbs-in |
| Recommended in-lb | |
| Material | Aluminum Alloy, Cast |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810337783 |
| UPC 12 Digit | 7818103377833 |

Dimensions

| | |
|---------------------------|---------|
| Dimension - B Length inch | 3.00 in |
| Dimension - Height mm | 0 mm |
| Dimension - Width inch | 3.00 in |
| Dimension - Width mm | 76 mm |

Conductor Related

| | |
|---------------------------|---|
| Conductor - ACSR Str Size | 954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil |
|---------------------------|---|

| | |
|---------------------------------|---|
| Conductor - ACSR Str Size Range | 954 (45/7) Rail kcmil-1033.5 (45/7) Ortolan kcmil |
| Conductor - AL Str Size | 1033 kcmil;1100 kcmil;1113 kcmil |
| Conductor - AL Str Size Range | 1033 kcmil-1113 kcmil |

Certifications And Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance | EX |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_S2GBPA_BUNDLED_SPACER_LineArt](#)
- [Sales Drawings - 10038254](#)
- [Specifications - S2GBP445A8](#)