

## Substation - Aluminum Rigid Spacer

By Burndy

Catalog # [S2GBP44A](#)



Two Conductor 18 IN Spacer, 795 kcmil-874 kcmil ACSR, 954 kcmil AAC.

### Application

Substation

### General

Catalog Number	S2GBP44A
Connector Type	Spacer
Installation Torque	480 lbs-in
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810142035
UPC 12 Digit	7818101420355

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.165 in
Dimension - Diameter Min Size inch	1.092 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Conductor Related

Conductor - ACSR Str Size	795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil
Conductor - ACSR Str Size Range	795 (54/7) Condor kcmil-874.5 (54/7) Crane kcmil
Conductor - AL Str Size	954 kcmil
Conductor - AL Str Size Range	954 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_S2GBPA\\_BUNDLED\\_SPACER\\_LineArt](#)  
[Sales Drawings - SD057446-01](#)  
[Specifications - S2GBP44A](#)