

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP483A](#)



Two Conductor 18 IN Spacer, 2050 kcmil ACSR, 2000 kcmil-2250 kcmil AAC.

Application

Substation

General

Connector Type	Spacer
Installation Torque Recommended in-lb	480 lbs-in
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810365991
UPC 12 Digit	7818103659911

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.737 in
Dimension - Diameter Min Size inch	1.632 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	2050 kcmil
Conductor - ACSR Str Size Range	2034.5 (72/7) Mockingbird kcmil
Conductor - AL Str Size	2000 kcmil;2250 kcmil
Conductor - AL Str Size Range	2000 kcmil-2250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - S2GBP483A_MODEL-PDF](#)
[3D Models - S2GBP483A_MODEL-STEP](#)
[3D Models - S2GBP483A_MODEL-IGES](#)
[Sales Drawings - SD057446-01](#)