

## Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # [S2GBP483A12](#)



Two Conductor 12 IN Spacer, 2050 kcmil ACSR, 2000 kcmil-2250 kcmil AAC, 550kV.

### Application

Substation

### General

Catalog Number	S2GBP483A12
Connector Type	Spacer
Installation Torque	480 lbs-in
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810219713
UPC 12 Digit	7818102197133

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.737 in
Dimension - Diameter Min Size inch	1.632 in
Dimension - Height mm	77 mm
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Conductor Related

Conductor - ACSR Str Size	2050 (76/19) kcmil
Conductor - ACSR Str Size Range	2050 (76/19) kcmil
Conductor - AL Str Size	2000 kcmil;2250 kcmil
Conductor - AL Str Size Range	2000 kcmil-2250 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_S2GBPA\\_BUNDLED\\_SPACER\\_LineArt](#)  
[Sales Drawings - 50070024](#)  
[Specifications - S2GBP483A12](#)