

Substation - Aluminum Rigid Spacer

By Burndy
 Catalog # [S2GBPA486A8](#)



Two Conductor 8 IN Spacer, 2156 kcmil-2167 kcmil ACSR, 2300 kcmil-2500 kcmil AAC.

Application

Substation

General

Catalog Number	S2GBPA486A8
Connector Type	Spacer
Installation Torque	480 lbs-in
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810306062
UPC 12 Digit	7818103060622

Dimensions

Dimension - B Length inch	4.00 in
Dimension - Height inch	3.06 in
Dimension - Height mm	72.6 mm
Dimension - L Length Overall mm	268 mm
Dimension - Length Overall inch	10.56 in
Dimension - Width inch	4.00 in
Dimension - Width mm	102 mm

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2300 kcmil;2500 kcmil
Conductor - AL Str Size Range	2300 kcmil-2500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_S2GBPAA_BUNDLED_CABLE_TAP_LineArt](#)
- [Sales Drawings - 50053617](#)
- [Specifications - S2GBPA486A8](#)