

Substation - Aluminum Rigid Spacer

By Burndy
 Catalog # [S2GBPA48A8](#)



Two Conductor Spacer, EHV, Accommodates: 1750 KCMIL - 2000 KCMIL AAC, 1590 KCMIL- 1780 KCMIL ACSR, 550 KV.

Application

Substation

General

Catalog Number	S2GBPA48A8
Connector Type	Spacer
Material	Aluminum Alloy
Physical Attribute - Pad Orientation	Straight
Plated	N
UPC	781810269633
UPC 12 Digit	7818102696333

Dimensions

Dimension - Height inch	8.13 in
Dimension - Height mm	207 mm
Dimension - L Length Overall mm	262 mm
Dimension - Length Overall inch	10.30 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	1590 (45/7) Lapwing kcmil;1590 (54/19) Falcon kcmil;1780 (54/19) kcmil;1780 (84/19) Chukar kcmil
Conductor - ACSR Str Size Range	1590 (45/7) Lapwing kcmil-1780 (84/19) Chukar kcmil
Conductor - AL Str Size	1750 kcmil;1800 kcmil;1900 kcmil;2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_S2GBPAA_BUNDLED_CABLE_TAP_LineArt](#)
- [Sales Drawings - 30003877](#)
- [Specifications - S2GBPA48A8](#)