

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R41ACG5](#)



Rigid Spacer, Accommodates: 795 KCMIL ASC.

Application

Substation

General

Catalog Number	S2R41ACG5
Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
One Wrench Installation	Y
Plated	N
UPC	621945167001
UPC 12 Digit	6219451670011

Dimensions

Dimension - Height inch	2.00 in
Dimension - Height mm	50.8 mm
Dimension - L Length Overall mm	191 mm
Dimension - Length Overall inch	7.50 in
Dimension - Width inch	2.00 in
Dimension - Width mm	51 mm

Conductor Related

Conductor - AL Str Size	795 KCMIL
Conductor - AL Str Size Range	795 KCMIL
Conductor - Connection Combination	Cable Spacer
Conductor Spacing	6 in
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - S2R41ACG5](#)