

## Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # S2R466



2 Bundle 6 IN Spacer, 1500 kcmil CU Cable.

### Application

Substation

### General

Catalog Number	S2R466
Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque	480 in-lb
Recommended in-lb	
Material	Copper Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	781810486023
UPC 12 Digit	7818104860233

### Dimensions

Dimension - B Length inch	2.00 in
Dimension - Height inch	2.29 in
Dimension - L Length Overall mm	201 mm
Dimension - Length Overall inch	7.91 in
Dimension - Width inch	2.00 in
Dimension - Width mm	51 mm

### Conductor Related

Conductor - Connection Combination	Cable Spacer
Conductor - Copper Str Size	1500 kcmil
Number of Conductors	2

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	15
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10101753](#)  
[Specifications - S2R466](#)