

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R46ACG1](#)



Rigid 4 IN Spacer, 1590 kcmil , 230kV.

Application

Substation

General

Catalog Number	S2R46ACG1
Connector Type	Spacer
Installation Torque	480 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810529874
UPC 12 Digit	7818105298744

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Height inch	2.80 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.88 in
Dimension - Width inch	2.00 in
Dimension - Width mm	51 mm

Conductor Related

Conductor - AL Str Size Range	1590 kcmil
Conductor - Connection Combination	Cable Spacer

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - S2R46ACG1_MODEL-STEP](#)
- [3D Models - S2R46ACG1_MODEL-IGES](#)
- [3D Models - S2R46ACG1_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - CSC015144-01](#)
- [Specifications - S2R46ACG1](#)