

# Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # [S2R47ACG1](#)



Two Conductor 15 IN Cable Spacer, 1.361 IN-1.545 IN Dia AL Cable, 345kV.

## Application

Substation

## General

Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque Recommended in-lb	660 LBS/in
Material	Aluminum Alloy
One Wrench Installation	Y
Plating Type	Unplated
UPC	621945113671
UPC 12 Digit	6219451136711

## Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.12 in
Dimension - L Length Overall mm	448 mm
Dimension - Length Overall inch	17.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

## Conductor Related

Conductor - AL Str Size Range	1.361 in-1.545 in
Conductor - Connection Combination	Cable Spacer
Conductor Spacing	15 in
Number of Conductors	2

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[3D Models - S2R47ACG1\\_MODEL-PDF](#)  
[3D Models - S2R47ACG1\\_MODEL-STEP](#)  
[3D Models - S2R47ACG1\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)