

## Substation - Aluminum Rigid Spacer

By Burndy  
 Catalog # [S2R484ACG3](#)



### Application

Substation

### General

Catalog Number	S2R484ACG3
Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque	660 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	781810424056
UPC 12 Digit	7818104240566

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.12 in
Dimension - Height mm	79.2 mm
Dimension - L Length Overall mm	397 mm
Dimension - Length Overall inch	15.62 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Conductor Related

Conductor - AL Str Size Range	2303 kcmil
Conductor - Connection Combination	Cable Spacer
Number of Conductors	2

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - CSC.013077-01](#)
- [Specifications - S2R484ACG3](#)