

## Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # S2R496A15S7HQ



Rigid 15 IN Spacer, 735kV.

### Application

Substation

### General

Catalog Number	S2R496A15S7HQ
Connector Type	Spacer
Installation Torque	660 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	781810480120
UPC 12 Digit	7818104801200

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	2.50 in
Dimension - Diameter Min Size inch	2.28 in
Dimension - Height inch	4.10 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	465 mm
Dimension - Length Overall inch	18.30 in
Dimension - Width inch	3.00 in

Dimension - Width mm 76 mm

### Conductor Related

Conductor - Connection Combination	Cable Spacer
Number of Conductors	2

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

### Product Assets

- [3D Models - S2R496A15S7HQ\\_MODEL-STEP](#)
- [3D Models - S2R496A15S7HQ\\_MODEL-IGES](#)
- [3D Models - S2R496A15S7HQ\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10086146](#)
- [Specifications - S2R496A15S7HQ](#)