

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R59RCG1](#)



Application

Substation

General

Catalog Number	S2R59RCG1
Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque	660 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	781810460245
UPC 12 Digit	7818104602455

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.00 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	400 mm
Dimension - Length Overall inch	15.76 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size Range	1843.2 kcmil
Conductor - Connection Combination	Cable Spacer
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - CSC012568-01](#)
[Specifications - S2R59RCG1](#)