

Substation - Aluminum Rigid Spacer

By Burndy

Catalog # [S3GBP445A](#)

Three Conductor Spacer, 1033.5 kcmil-1113 kcmil AAC, 954(45/7) kcmil-1033.5(45/7) kcmil ACSR, 550kV.



Application

Substation

General

Catalog Number	S3GBP445A
Connector Type	Spacer
Installation Torque	480 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810246092
UPC 12 Digit	7818102460922

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.216 in
Dimension - Diameter Min Size inch	1.165 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil
---------------------------	-----------------------------------------------------------------------------

Conductor - ACSR Str Size Range	954 (45/7) Rail kcmil-1033.5 (45/7) Ortolan kcmil
Conductor - AL Str Size	1033 kcmil;1100 kcmil;1113 kcmil
Conductor - AL Str Size Range	1033 kcmil-1113 kcmil
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeACSR C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_S3GBPA_SPACER_3CONDUCTOR_LineArt](#)
[Sales Drawings - 30007567](#)
[Specifications - S3GBP445A](#)