

# Substation - Aluminum Rigid Spacer

By Burndy  
Catalog # [S3GBP44A](#)



## Application

Substation

## General

Catalog Number	S3GBP44A
Connector Type	Spacer
Installation Torque	480 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810276730
UPC 12 Digit	7818102767300

## Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.126 in
Dimension - Diameter Min Size inch	1.092 in
Dimension - Height mm	0 mm
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

## Conductor Related

Conductor - ACSR Str Size	795 (54/7) Condor kcmil;795 (24/7) kcmil
---------------------------	--

Conductor - ACSR Str Size Range	795 (54/7) Condor kcmil-795 (24/7) kcmil
Conductor - AL Str Size	954 kcmil
Conductor - AL Str Size Range	954 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• ACSR C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_S3GBPA\\_SPACER\\_3CONDUCTOR\\_LineArt](#)
- [Sales Drawings - 30007567](#)
- [Specifications - S3GBP44A](#)