

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBP45A](#)

Three Conductor Spacer, 1192 kcmil-1272 kcmil AAC,
1033.5(54/7) kcmil-1192.5(54/19) kcmil ACSR, 550kV.



Application

Substation

General

Catalog Number	S3GBP45A
Connector Type	Spacer
Installation Torque	480 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810209820
UPC 12 Digit	7818102098200

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.333 in
Dimension - Diameter Min Size inch	1.246 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil
Conductor - ACSR Str Size Range	1033.5 (54/7) Curlew kcmil-1192.5 (54/19) Grackle kcmil
Conductor - AL Str Size	1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil
Conductor - AL Str Size Range	1192 kcmil-1272 kcmil
Conductor Type	<ul style="list-style-type: none"> AL C Str-Size ACSR C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_S3GBPA_SPACER_3CONDUCTOR_LineArt](#)
- [Sales Drawings - 30007567](#)
- [Specifications - S3GBP45A](#)