

Substation - Aluminum Rigid Spacer

By Burndy
 Catalog # [S3GBP486A](#)



Three Conductor Spacer, 2300 kcmil-2500 kcmil AAC, 2167(72/7) kcmil-2156(84/19) kcmil ACSR, 550kV.

Application

Substation

General

Catalog Number	S3GBP486A
Connector Type	Spacer
Installation Torque	480 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810259993
UPC 12 Digit	7818102599933

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.823 in
Dimension - Diameter Min Size inch	1.737 in
Dimension - Height mm	0 mm
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	2156 (64/119) kcmil;2156 (84/19) Bluebird kcmil;2167
---------------------------	--

Conductor - ACSR Str Size Range	(72/7) Kiwi kcmil 2156 (64/119) kcmil-2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2300 kcmil;2500 kcmil
Conductor - AL Str Size Range	2300 kcmil-2500 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • ACSR C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_S3GBPA_SPACER_3CONDUCTOR_LineArt](#)
- [Sales Drawings - 30007567](#)
- [Specifications - S3GBP486A](#)